


Users Guidelines & Care Instructions for Swiss Shield®

Thank you for purchasing our Swiss Shield® EMC fabrics. We hope it will provide you with years of satisfying use. For optimal results and product longevity, please read this document in full before you attempt installation. For more information or if you have any further questions please contact your authorized support representative for assistance.

- Swiss Shield® fabric is designed to reduce Radio Frequency exposure on the principle of reflection. The fabrics are available in 2 formats non-conductive and conductive and there are several models of each format. Regardless of format or model, each fabric contains a patented arrangement of wire mesh, interwoven tiny silver coated copper threads that are sealed to the touch and to the elements. All Swiss Shield® fabrics can be washed without shielding loss unlike most other brands.



Swiss Shield® Thread

- Surface Conductive or Surface Insulated Thread
- Base Material (Cotton or Synthetic)



Surface Insulated


New Daylite
Naturell
Wear
Ultima

Surface Conductive

Evo Ultra
Naturell Ultra
Condex – Not available

- When Swiss Shield® fabric is installed, its location, quantity and proper installation should be determined by a trained EMF specialist or consultant. If a specialist or consultant is not available in your area then appropriate measuring equipment should be acquired by the user. Please review our EMF Meter, RF Meter and Body Voltage Kit product pages for details.
- In order to ensure optimum results, the installer/user should assess the living space for Radio Frequency “RF” Radiation and AC Electric Fields. Before and after measurements are important to determine the overall effectiveness and impact of the shield. **Important:** We recommend that larger pieces of fabric and canopies of non-conductive fabrics should be installed in a low AC Electric Field environment (>1 V/m or >100 mV of body voltage). Usually the shutting off of circuit breakers or the installation of a Remote Cutoff Switch is required.
- In addition to blocking RF, grounding the conductive fabric can aid in the reduction of AC electric fields. In the event that a ground is applied to the Swiss Shield® fabric, please consult with your local licensed electrician and comply with local electrical codes. Note: Swiss Shield® will reflect radio waves whether grounded or not. The Swiss Shield® non-conductive fabrics are not externally conductive and grounding is not recommended. Before and after measurements are important to determine the overall effectiveness and impact of the shield.
- Avoid the use of electronic or electrical devices near the fabric or under a canopy.
- Swiss Shield® fabric is not fire retardant. Use with caution and at your own risk.
- Swiss Shield® fabric is intended exclusively for indoor use in dry areas.
- Swiss Shield® fabrics have the Oeko-Tex 100 certification meaning they are the highest quality and most Eco friendly shielding fabric available. As with all new textile fabric, a “new material” scent may exist. The impact of this scent varies from person to person. Washing the material before installation will eliminate the scent.

Sewing - Use regular thread and a felled seam to join pieces



Washing: Use a Mild Liquid Detergent



TESTEX AG, Swiss Textile Testing Institute

Institute of the International Association for Research and Testing in the Field of Textile Ecology



The company

SPOERRY 1866 AG

Bergstrasse 25
CH - 8890 Flums

is granted authorisation according to Oeko-Tex® Standard 100 to use the Oeko-Tex® mark, based on **test report ZH005 123343.1**



Tested for harmful substances
according to Oeko-Tex® Standard 100
ZH005 070054
TESTEX

for the following articles:

- Swiss Shield Yarn; textile filament Brass/Silver TWF-D, Copper/Silver textile filament TW-F (Polyamidimid), braided with polyester or cotton yarns);**
- Covered raw yarn made of polyamide/elastane (based on material pre-certified according to Oeko-Tex® Standard 100)**

The results of the inspection made according to Oeko-Tex® Standard 100, product class I for baby articles, have shown that the above mentioned goods meet the human-ecological requirements of the standard presently established.

The certified articles fulfil the requirements of Annex XVII of REACH (incl. the use of azo-dyes, nickel, etc.) as well as the American requirement regarding total content of lead in children's articles (CPSIA), with the exception of accessories made from glass).

The holder of the certificate, who has issued a conformity declaration according to EN ISO 17060-1, is obliged to use the Oeko-Tex® mark only in conjunction with products that are conform with the sample initially tested. The conformity is verified by audits.

This authorisation is valid until 15.07.2017


Zurich, 21.10.2016



Serge Rolle
Serge Rolle
CEO

Ell Lorenzen
Ell Lorenzen
Manager Analytical Testing

CERTIFICATE



Comparison of Swiss Shield Fabrics RF Shielding Performance - 1 Layer